



## MT-BRONZE @df

MT-BRONZE @df is our 80% bronze filled filament which is easy to print, sand & polish. With MT-BRONZE @df you can create the most beautiful objects with real METAL characteristics, such as a 3 x higher weight then PLA @df, a METAL feel & touch and thermo-conductivity. Due to the high percentage of fillers MT-BRONZE @df has virtually no shrinkage. A special lubricant increases the flow and prevents MT-BRONZE @df to adhere to the nozzle. Finally all above combined with the correct hardness results in a filament that can be printed on almost every type of FDM 3d printer available on the market with retraction enabled on nozzles  $\geq 0.35$  mm.

### Features:

- Approx. 80% bronze content
- PLA-based, 3 times heavier
- Metal feel & “cold” touch
- Excellent printability on both direct & Bowden style 3D printers
- Processing additive added for easy & reliable printing
- Quick & easy polishing and other post-processing
- Possibility to print with retraction
- Works on nozzles  $\geq 0.35$  mm

### Dimensions

Size	Ø tolerance	roundness
1,75mm	$\pm 0,05$ mm	$\geq 95\%$
2,85mm	$\pm 0,10$ mm	$\geq 95\%$

### Physical properties

Description	Testmethod	Typical value
Specific gravity	ISO 1183	3,39 g/cc
MFI	-	n.a.
Yield stress (50mm/min)	ISO 527	18,3 MPa
Strain at break (50mm/min)	ISO 527	8,0%
Tensile (E) modulus (1mm/min)	ISO 527	3990 Mpa
Impact strength, Izod unnotched 23°C	ISO 180/A	11,3 KJ/m <sup>2</sup>



Printed

Sanded & Polished

Patinated

### MT @df range:

MT-BRONZE @df is available from stock in it's natural bronze colour. For other METALS have a look at our website.



### Thermal Properties

Description	Testmethod	Typical value
printing temp.	DF	195-220 °C
mellting temp.	ISO 294	195°C $\pm$ 10°C
vicat softening temp.	ISO 306	$\pm 65$ °C

### Packaging:

MT-BRONZE @df is available in nearly any type of packaging and labelling. Keep in mind the high density of the product to select the preferred amount per reel. Ask our team to help you customizing your product.

### Additional info:

MT-BRONZE @df can be printed without a heated bed, but if you do have a heated bed the recommended temperature is  $\pm 35-60$ °C. Storage: Cool and dry (15-25°C) and away from UV light. This enhances the shelf life significantly.

MT-BRONZE @df can be used on all common desktop FDM or FFF technology 3D printers.

\* Please consider the use of a hardened steel nozzle when printing with MT-BRONZE @df.

The bronze powder inside makes the filament abrasive and will result in fast wear of regular brass nozzles.

\* Please have a look at the Printing, post-processing & other info document for further tips & tricks.